




DCS32-22MM-1/2"-A

Ruland DCS32-22MM-1/2"-A, 22mm x 1/2" Single Disc Coupling, Aluminum, Clamp Style, 2.000" (50.8mm) OD, 1.813" (46.1mm) Length





Description

Ruland DCS32-22MM-1/2"-A is a clamp single disc coupling with 22mm x 0.5000" bores, 2.000" (50.8mm) OD, and 1.813" (46.1mm) length. It is zero-backlash and has a balanced design for reduced vibration at high speeds. The single disc design is comprised of two anodized aluminum hubs and two sets of thin stainless steel disc springs which can accommodate angular misalignment and axial motion, however does not allow for any parallel misalignment. DCS32-22MM-1/2"-A is lightweight and has low inertia making it well suited for applications with speeds up to 10,000 RPM. Hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. Ruland manufactures DCS32-22MM-1/2"-A to be torisionally rigid and an excellent fit for precise positioning stepper servo applications commonly found in semiconductor, solar, printing, machine tool, and test and measurement systems. It is machined from solid bar stock that is sourced exclusively from North American mills and RoHS3 and REACH compliant. DCS32-22MM-1/2"-A is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Bore (B1)	22 mm	Small Bore (B2)	0.5000 in
31 Max Shaft Penetration	0.874 in (22.2 mm)	B2 Max Shaft Penetration	0.874 in (22.2 mm)
Outer Diameter (OD)	2.000 in (50.8 mm)	Bore Tolerance	+0.001 in / -0.000 in (+0.03 mm /
			-0.00 mm)
_ength (L)	1.813 in (46.1 mm)	Hub Width (LH)	0.810 in (20.55 mm)
Recommended Shaft Tolerance	+0.0000 / -0.0005 " (+0.000 / -0.013	3 Forged Clamp Screw	M5
	mm)		
Screw Material	Alloy Steel	Hex Wrench Size	4.0 mm
Screw Finish	Black Oxide	Seating Torque	9.5 Nm
Number of Screws	2 ea	Dynamic Torque Reversing	87.5 lb-in (9.90 Nm)
Angular Misalignment	1.0°	Dynamic Torque Non-Reversing	175 lb-in (19.80 Nm)
Parallel Misalignment	0.000 in (0.00 mm)	Static Torque	350 lb-in (39.6 Nm)
Axial Motion	0.012 in (0.30 mm)	Torsional Stiffness	867 lb-in/Deg (98.0 Nm/Deg)
Moment of Inertia	0.2531 lb-in ² (7.407 x 10 ⁻⁵ kg-m ²)	Maximum Speed	10,000 RPM
Full Bearing Support Required?	Yes	Zero-Backlash?	Yes
Balanced Design	Yes	Torque Wrench	TW:BT-4C-3/8-86
Recommended Hex Key	Metric Hex Keys	Material Specification	Hubs: 2024-T351 Aluminum Bar,
			Disc Springs: Type 302 Stainless
			Steel
Temperature	-40°F to 200°F (-40°C to 93°C)	Finish Specification	Sulfuric Anodized MIL-A-8625 Type
			II, Class 2 and ASTM B580 Type B Black Anodize
Manufacturer	Ruland Manufacturing	Country of Origin	USA
Weight (lbs)	0.436900	UPC	634529152263
Fariff Code	8483.60.8000	UNSPC	31163008
Note 1	Stainless steel hubs are available u	*****	01100000
Note 2	Torque ratings are at maximum misalignment.		
Note 3	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
NOIE 3	Torque ratings for the couplings are based on the physical limitations/failure point of the disc springs. Under		

shaft is possible below the rated torque of the disc springs. Keyways are available to provide additional torque capacity in the shaft/hub connection when required. Please consult technical support for more assistance.

Prop 65

MARNING This product can expose you to chemicals including Ethylene Thiourea and Nickel (metallic), known to the State of California to cause cancer, and Ethylene Thiourea known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

Installation Instructions

- 1. Align the bores of the DCS32-22MM-1/2"-A single disc coupling on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (*Angular Misialignment*: 1.0°, *Parallel Misalignment*: 0.00 in (0.00 mm), *Axial Motion*: 0.012 in (0.30 mm))
- 2. Fully tighten the M5 screw on the first hub to the recommended seating torque of 9.5 Nm using a 4.0 mm hex torque wrench.
- 3. Before tightening the screw on the second hub, rotate the coupling by hand to allow it to reach its free length.
- 4. Tighten the screw on the second hub to the recommended seating torque. Make sure the coupling remains axially relaxed and the misalignment angle remains centered along the length of the coupling.
- 5. The shafts may extend into the relieved portion of the bore as long as it does not exceed the shaft penetration length of 0.874 in (22.2 mm).